

Solid Edge Simulation

Embedded finite element analysis for design engineers

Benefits

- Innovate more by experimenting with designs virtually
- Optimize material usage and minimize product weight
- Reduce the need for costly prototypes with virtual testing
- Get products to market faster with reduced physical testing
- Reduce recalls by finding out if products fail before it reaches the customer
- Execute redesigns faster with synchronous technology

Features


- Embedded finite element analysis for design engineers
- Automatic finite element model creation with optional manual override
- Realistic operating environment modeling with full complement of loads and constraint definitions
- Evaluate designs for deformation, stress, resonant frequencies, buckling, heat transfer thermal stress and vibration response
- Ability to maintain loads and constraints during model changes

Summary

Siemens Solid Edge® Simulation software is an easy-to-use, built-in finite element analysis (FEA) tool that enables design engineers to digitally validate part and assembly designs within the Solid Edge environment. Based on proven Simcenter Femap™ finite element modeling technology, Solid Edge Simulation significantly reduces the need for physical prototypes, reducing material and testing costs, while saving design time.

For use by design engineers

Solid Edge Simulation uses the same underlying geometry and user interface as all Solid Edge applications. It's easy enough for any Solid Edge user with a fundamental understanding of FEA principles, yet robust enough to service almost any analysis need. By enabling engineers to perform their own simulation, more analysis can be performed in less time — improving quality, reducing material costs and minimizing the need for physical prototypes — without incurring the high costs of outsourced analysis. The layout of the user interface is designed to guide the user through the entire analysis process, with help available if needed, which makes it easy to learn initially, and revisit if necessary.



Solid Edge Simulation

Features *continued*

- Import fluid pressure and temperature results from Simcenter FLOEFD for Solid Edge
- Embedded advanced motion simulation


Automatic finite element model creation

Solid Edge Simulation supports solid meshes (using tetrahedral elements), two-dimensional shell element meshes on mid-surfaced sheet structures, hybrid models that contain both 2D shell and 3D solid elements, as well as 1D beam elements for frame structures. Users can create and refine finite element meshes where required to improve accuracy of results.

A mesh size slider bar that makes element size adjustments to the overall finite element mesh is available with additional control of the number of elements on individual edges and faces. With Solid Edge Simulation, you can leverage a mapped mesh capability to take advantage of certain geometry topologies and create a more orderly and well-shaped mesh. In addition, the mesh size will automatically adjust to accommodate detailed model features. You can fine-tune the mesh with manual edge and face element sizing to generate an efficient simulation model that will deliver accurate results. Prior to creating the finite element model, you can prepare and simplify the geometry model quickly and easily with synchronous technology and its ability to make history-free model changes. Solid Edge synchronous technology combines the speed and simplicity of direct modeling with the flexibility and control of parametric design.

Full complement of load and constraint definitions

Solid Edge Simulation provides all boundary condition definitions needed to define realistic operating environments. The constraints are geometry-based and include fixed, pinned, no



rotation, symmetric and cylindrical variations. The loads are also geometry-based and include mechanical as well as temperature loading for thermal analyses. Mechanical loads include forces, pressures and effects caused by body rotation and gravity. Solid Edge Simulation facilitates load and constraint applications with Quick Bar input options and handles for direction and orientation definition.

Analyzing assemblies

Assembly model components can quickly be connected, and interaction can be a glued connection between components or surface contacts based on an iterative linear solution.

Contact between components can be detected automatically, or connectors can be defined individually through manual face selection. Assembly materials and properties can be applied manually, selected from a material library or inherited from the geometry model by default. The included Simcenter™ Nastran® solver assures realistic assembly/component interaction to facilitate robust solutions.

Solid Edge Simulation offers complete control of the management of geometries in a simulation study. Components can easily be suppressed or removed from a study to maximize efficiency, improving user experience.

Analysis types

Using the industry-standard Simcenter Nastran solver, Solid Edge Simulation delivers structural simulation results, such as deformation, stress and strain, etc. caused by a static loading, finding the natural frequencies of vibration or determining buckling loads of a design. Both steady and transient heat transfer analysis validate cooling performance by evaluating the temperature distribution of the model. In addition, the coupled thermal and structural analysis can be applied to determine thermal effects to the structural stress/strain.

Fluid pressure and temperature results can be imported from Simcenter FLOEFD™ for Solid Edge as structural loads for analysis. FLOEFD for Solid Edge delivers the industry's leading computational fluid dynamics (CFD) analysis tool for fluid flow and heat transfer. Integration between the two simulation solutions is seamless and easy, as both are fully embedded in the Solid Edge environment.

Harmonic response analysis, dynamic response analysis in frequency domain, is also available to simulate the actual vibration level. Re-use of finite element model loads and constraints is as easy as dragging and dropping from one study to another.

Designs in motion

With dynamic motion simulation, Solid Edge Simulation allows you to evaluate and visualize how parts will interact in an assembly. The easy-to-use solution simulates how a product will perform throughout its operational cycle, allowing you to see how it would function in the real world and measure the forces and loads on the design.

Solid Edge Simulation offers you the ability to create motion models from existing Solid Edge assemblies. Mechanical joints can easily be created by either automatically converting them from assembly constraints, or by using the intuitive builder which walks you through the process step-by-step. Motion characteristics can then be added, including motors, actuators, gravity, realistic contact between bodies, springs, friction, damping and other generated forces as needed. Additionally, motion results, such as forces, can be utilized as load conditions for structural simulation.

Scalable solutions for every user

Powerful, scalable solution offerings allow you to select the best simulation tools for your individual requirements.


Result evaluation

Solid Edge Simulation allows you to interpret and understand the resulting model behavior quickly with comprehensive graphical result viewing tools. Simulation results can be displayed in various forms, including color and contour plots, which can be continuous, displayed as distinct contour bands or by element and displacement and mode shapes that can be animated. Minimum/maximum stress markers and a probe tool with results displays are also available. The probe tool can select nodes, faces and edges.

With Solid Edge Simulation’s comprehensive results evaluation functionality, you can quickly identify problem areas for potential design revision and generate HTML reports of simulation model information and final results.

Design updates

With Solid Edge Simulation, you can quickly and easily make any required design update during post analysis. History-free, feature-based model changes with synchronous technology significantly accelerates the model



	Solid Edge Premium	Solid Edge Simulation	
		Standard	Advanced
Simulation Modeling and Results Evaluation	X	X	X
Linear Static	X	X	X
Advanced Motion	X	X	X
Optimization (Shape/Parameters)	X	X	X
Normal Modes		X	X
Buckling		X	X
Heat Transfer - Steady State			X
Heat Transfer - Transient			X

refinement process. In addition, Solid Edge Simulation maintains associativity between the CAD and finite element models, while making sure that applied loads and constraints are maintained for all geometry model changes.

Analysis scalability

Simulation functionality scales from application to individual parts to analysis of large assemblies, all the way to Femap with Nastran, thereby enabling you to define and analyze complete systems. This complete line of products provides a scalable upgrade path for users who need to solve more challenging engineering problems. Complete geometry and finite element models with boundary conditions and results can be seamlessly transferred from Solid Edge to Femap, where more advanced analyses can be employed if desired.

Extending value

Solid Edge is a portfolio of affordable, easy to deploy, maintain and use software tools that advance all aspects of the product development process -- mechanical and electrical design, simulation, manufacturing, technical documentation, data management and cloud-based collaboration.

Minimum system configuration

- Windows 10 Enterprise or Professional (64-bit only) version 1809 or later
- 16 GB RAM
- 65K colors
- Screen resolution: 1920 x 1080
- 8.5 GB of disk space required for installation

Siemens Digital Industries Software
www.sw.siemens.com

Americas +1 314 264 8499
Europe +44 (0) 1276 413200
Asia-Pacific +852 2230 3333